


## HF3 Relay

- Y-Design
- Frequency range DC to 3GHz
- Impedance 50Ω or 75Ω
- Small dimensions (14.6x7.2x10mm)
- 1 form C contact (1 changeover contact)
- Immersion cleanable
- Low power consumption (≤140mW)

### Typical applications

Cable modems and linecards/ CATV, Tabs, measurement and test equipment ATE, satellite / audio / video tuners, wireless base stations and antennas, switching boards



### Contact Data

|                                   |                              |
|-----------------------------------|------------------------------|
| Contact arrangement               | 1 form C, 1 CO               |
| Max. switching voltage            | 220VDC, 250VAC               |
| Rated current                     | 2A                           |
| Limiting continuous current, 23°C | 2A                           |
| Switching power                   | 60W, 62.5VA,<br>50W (2.5GHz) |
| Max. continuous RF-power, 23°C    | 50W (2.5GHz)                 |
| Contact material                  | Ag, Au covered               |
| Minimum switching voltage         | 100μV                        |
| Initial contact resistance        | <100mΩ at 10mA, 30mV         |
| Operate time                      | typ. 3ms, max. 5ms           |
| Release time                      |                              |
| without diode in parallel         | typ. 2ms, max. 5ms           |
| with diode in parallel            | typ. 4ms, max. 6ms           |
| Bounce time                       | typ. 1ms, max. 3ms           |
| Duration of set/reset pulse min.  | 20ms                         |
| Mechanical endurance              | 10 <sup>7</sup> operations   |

### Coil Data

|                    |            |
|--------------------|------------|
| Coil voltage range | 3 to 24VDC |
|--------------------|------------|

### Coil versions, monostable

| Coil code                              | Rated voltage VDC | Operate voltage VDC | Limiting voltage VDC | Release voltage VDC | Coil resistance Ω±10% | Rated coil power mW |
|----------------------------------------|-------------------|---------------------|----------------------|---------------------|-----------------------|---------------------|
| <b>50Ω version, monostable, 1 coil</b> |                   |                     |                      |                     |                       |                     |
| 51                                     | 3                 | 2.25                | 6.50                 | 0.30                | 64                    | 140                 |
| 52                                     | 4.5               | 3.38                | 9.80                 | 0.45                | 145                   | 140                 |
| 53                                     | 5                 | 3.75                | 10.90                | 0.50                | 178                   | 140                 |
| 54                                     | 6                 | 4.50                | 13.00                | 0.60                | 257                   | 140                 |
| 55                                     | 9                 | 6.75                | 19.60                | 0.90                | 574                   | 140                 |
| 56                                     | 12                | 9.00                | 26.10                | 1.20                | 1028                  | 140                 |
| 57                                     | 24                | 18.00               | 52.30                | 2.40                | 4114                  | 140                 |
| <b>75Ω version, monostable, 1 coil</b> |                   |                     |                      |                     |                       |                     |
| 01                                     | 3                 | 2.25                | 6.50                 | 0.30                | 64                    | 140                 |
| 02                                     | 4.5               | 3.38                | 9.80                 | 0.45                | 145                   | 140                 |
| 03                                     | 5                 | 3.75                | 10.90                | 0.50                | 178                   | 140                 |
| 04                                     | 6                 | 4.50                | 13.00                | 0.60                | 257                   | 140                 |
| 05                                     | 9                 | 6.75                | 19.60                | 0.90                | 574                   | 140                 |
| 06                                     | 12                | 9.00                | 26.10                | 1.20                | 1028                  | 140                 |
| 07                                     | 24                | 18.00               | 52.30                | 2.40                | 4114                  | 140                 |

All figures are given for coil without pre-energization, at ambient temperature +23°C.

### Coil Data (continued)

#### Coil versions, bistable

| Coil code                             | Rated voltage VDC | Set voltage VDC | Limiting voltage VDC | Reset voltage VDC | Coil resistance Ω±10% | Rated coil power mW |
|---------------------------------------|-------------------|-----------------|----------------------|-------------------|-----------------------|---------------------|
| <b>50Ω version, bistable, 1 coil</b>  |                   |                 |                      |                   |                       |                     |
| 71                                    | 3                 | 2.25            | 9.20                 | -2.25             | 128                   | 70                  |
| 72                                    | 4.5               | 3.38            | 13.85                | -3.38             | 289                   | 70                  |
| 73                                    | 5                 | 3.75            | 15.30                | -3.75             | 357                   | 70                  |
| 74                                    | 6                 | 4.50            | 18.50                | -4.50             | 514                   | 70                  |
| 75                                    | 9                 | 6.75            | 27.70                | -6.75             | 1157                  | 70                  |
| 76                                    | 12                | 9.00            | 37.00                | -9.00             | 2057                  | 70                  |
| 77                                    | 24                | 18.00           | 74.00                | -18.00            | 8228                  | 70                  |
| <b>50Ω version, bistable, 2 coils</b> |                   |                 |                      |                   |                       |                     |
| 91                                    | 3                 | 2.25            | 6.50                 | 2.25              | 64                    | 140                 |
| 92                                    | 4.5               | 3.38            | 9.80                 | 3.38              | 145                   | 140                 |
| 93                                    | 5                 | 3.75            | 10.90                | 3.75              | 178                   | 140                 |
| 94                                    | 6                 | 4.50            | 13.00                | 4.50              | 257                   | 140                 |
| 95                                    | 9                 | 6.75            | 19.60                | 6.75              | 574                   | 140                 |
| 96                                    | 12                | 9.00            | 26.10                | 9.00              | 1028                  | 140                 |
| 97                                    | 24                | 18.00           | 52.30                | 18.00             | 4114                  | 140                 |

All figures are given for coil without pre-energization, at ambient temperature +23°C.

### Coil Data (continued)



#### Coil versions, bistable

| Coil code                             | Rated voltage VDC | Set voltage VDC | Limiting voltage VDC | Reset voltage VDC | Coil resistance Ω±10% | Rated coil power mW |
|---------------------------------------|-------------------|-----------------|----------------------|-------------------|-----------------------|---------------------|
| <b>75Ω version, bistable, 1 coil</b>  |                   |                 |                      |                   |                       |                     |
| 21                                    | 3                 | 2.25            | 9.20                 | -2.25             | 128                   | 70                  |
| 22                                    | 4.5               | 3.38            | 13.85                | -3.38             | 289                   | 70                  |
| 23                                    | 5                 | 3.75            | 15.30                | -3.75             | 357                   | 70                  |
| 24                                    | 6                 | 4.50            | 18.50                | -4.50             | 514                   | 70                  |
| 25                                    | 9                 | 6.75            | 27.70                | -6.75             | 1157                  | 70                  |
| 26                                    | 12                | 9.00            | 37.00                | -9.00             | 2057                  | 70                  |
| 27                                    | 24                | 18.00           | 74.00                | -18.00            | 8228                  | 70                  |
| <b>75Ω version, bistable, 2 coils</b> |                   |                 |                      |                   |                       |                     |
| 41                                    | 3                 | 2.25            | 6.50                 | 2.25              | 64                    | 140                 |
| 42                                    | 4.5               | 3.38            | 9.80                 | 3.38              | 145                   | 140                 |
| 43                                    | 5                 | 3.75            | 10.90                | 3.75              | 178                   | 140                 |
| 44                                    | 6                 | 4.50            | 13.00                | 4.50              | 257                   | 140                 |
| 45                                    | 9                 | 6.75            | 19.60                | 6.75              | 574                   | 140                 |
| 46                                    | 12                | 9.00            | 26.10                | 9.00              | 1028                  | 140                 |
| 47                                    | 24                | 18.00           | 52.30                | 18.00             | 4114                  | 140                 |

All figures are given for coil without pre-energization, at ambient temperature +23°C.

## HF3 Relay (Continued)

### Coil operating Range



### RF Data

|                                    |                |                |
|------------------------------------|----------------|----------------|
| Isolation                          |                |                |
| at 100MHz/900MHz                   | 80dB/72dB      | 80dB/72dB      |
| at 3GHz                            | 45dB           | 40dB           |
| Insertion loss                     |                |                |
| at 100MHz/900MHz                   | 0.03dB/0.12dB  | 0.03dB/0.12dB  |
| at 3GHz                            | 0.35dB         | 0.40dB         |
| Voltage standing wave ratio (VSWR) |                |                |
| at 100MHz/900MHz/3GHz              | 1.05/1.20/1.20 | 1.05/1.20/1.40 |

### Other Data

Material compliance: EU RoHS/ELV, China RoHS, REACH, Halogen content refer to the Product Compliance Support Center at [www.te.com/customer-support/rohssupportcenter](http://www.te.com/customer-support/rohssupportcenter)

|                                                  |                                     |
|--------------------------------------------------|-------------------------------------|
| Ambient temperature                              | -55°C to +85°C                      |
| Thermal resistance                               | <165K/W                             |
| Category of environmental protection             |                                     |
| IEC 61810                                        | RT III - wash tight                 |
| Degree of protection, IEC 60529                  | IP 67, immersion cleanable          |
| Vibration resistance (functional)                | 35g, 10 to 1000Hz                   |
| Shock resistance (functional), half sinus 11ms   | 50g                                 |
| Shock resistance (destructive), half sinus 0.5ms | 150g                                |
| Terminal type                                    | SMT                                 |
| Weight                                           | max. 2.5g                           |
| Resistance to soldering heat SMT                 | Peak Value                          |
| IEC 60068-2-58                                   | 265°C                               |
| Moisture sensitive level, JEDEC J-Std-020D       | MSL3                                |
| Ultrasonic cleaning                              | not recommended                     |
| Packaging/unit                                   | reel/400 pcs., box/400 or 2000 pcs. |

### Insulation Data

#### 50Ω version 75Ω version

|                                 |                      |
|---------------------------------|----------------------|
| Initial dielectric strength     |                      |
| between open contacts           | 600V <sub>rms</sub>  |
| between contact and coil        | 1000V <sub>rms</sub> |
| Initial surge withstand voltage |                      |
| between open contacts           | 1000V                |
| between contact and coil        | 1500V                |